

**IE-BP-VAPP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

For protecting your devices against dust and dirt.

**General ordering data**

Version	Flange-mounted housing, protective cap
Order No.	<a href="#">1068930000</a>
Type	IE-BP-VAPP
GTIN (EAN)	4032248823093
Qty.	10 pc(s).

**IE-BP-VAPP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	19.5 mm	Depth (inches)	0.768 inch
Net weight	11 g		

**Temperatures**

Operating temperature	-40 °C...70
-----------------------	-------------

**General data**

Colour	black	Protection degree	IP54
Type of mounting	Indoors only	UL 94 flammability rating	V-0

**Classifications**

ETIM 6.0	EC002314	ETIM 7.0	EC002314
ETIM 8.0	EC002314	ETIM 9.0	EC002314
ECLASS 9.0	27-44-02-08	ECLASS 9.1	27-44-02-08
ECLASS 10.0	27-44-02-08	ECLASS 11.0	27-44-02-08
ECLASS 12.0	27-44-02-08	ECLASS 13.0	27-44-02-08

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

## IE-BP-VAPP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

