

**IE-PIC-HYB-S-0,75-300****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Hybrid, 10-pole. Inserts for plug-in connectors Variant 14

**General ordering data**

Version	Crimp contact, for plug insert, Hybrid
Order No.	<a href="#">1068950000</a>
Type	IE-PIC-HYB-S-0,75-300
GTIN (EAN)	4032248823109
Qty.	300 pc(s).

**IE-PIC-HYB-S-0,75-300****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	0.27 g
------------	--------

**General data**

Wire connection cross section, finely stranded, max.	0.75 mm <sup>2</sup>	Wire connection cross section, finely stranded, min.	0.75 mm <sup>2</sup>
--	----------------------	--	----------------------

**Electrical properties**

Rated voltage	24 V
---------------	------

**Classifications**

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ETIM 9.0	EC001121
ECLASS 9.0	27-44-03-90	ECLASS 9.1	27-44-09-90
ECLASS 10.0	27-44-03-90	ECLASS 11.0	27-44-03-90
ECLASS 12.0	27-44-03-90	ECLASS 13.0	27-44-03-90

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Important note**

Product information	Hybrid, 10-pole. Inserts for plug-in connectors Variant 14
---------------------	--

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a> <a href="#">Designation key / Type key</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

## IE-PIC-HYB-S-0,75-300

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Dimensioned drawing

