

**IE-PI-HYB-10P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Hybrid, 10-pole. Inserts for plug-in connectors Variant 14

**General ordering data**

Version	Insert, for plug insert, Hybrid
Order No.	<a href="#">1068990000</a>
Type	IE-PI-HYB-10P
GTIN (EAN)	4032248823963
Qty.	1 pc(s).

## IE-PI-HYB-10P

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	16.29 g
------------	---------

## Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

## General data

Category	Cat.5 (ISO/IEC 11801)	Connection 1	Hybrid (Q10)
Connection 2	Crimp	Housing main material	Nickel silver, PA 66
Insulation cross-section, max.	2.2 mm	Insulation cross-section, min.	1 mm
Plugging cycles	500	Protection degree	IP67 with housing
Shielding	360°; all-round enclosure	Wire connection cross section, finely stranded, max.	0.75 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	0.08 mm <sup>2</sup>	Wire cross-section, finely stranded, max. (AWG)	AWG 20
Wire cross-section, finely stranded, min. (AWG)	AWG 27		

## Electrical properties

Contact resistance	≤ 5 mΩ	Rated current	3 A per contact
Rated voltage	24 V	Volume resistance	<10 mΩ

## General standards

Certificate no. (cULus)	E316369
-------------------------	---------

## Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ETIM 9.0	EC001121
ECLASS 9.0	27-44-03-90	ECLASS 9.1	27-44-09-90
ECLASS 10.0	27-44-03-90	ECLASS 11.0	27-44-03-90
ECLASS 12.0	27-44-03-90	ECLASS 13.0	27-44-03-90

## Important note

Product information	Hybrid, 10-pole. Inserts for plug-in connectors Variant 14
---------------------	--

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E316369

## IE-PI-HYB-10P

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">DUXR.E316369</a> <a href="#">PROFINET Manufacturer's Declaration</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a> <a href="#">Designation key / Type key</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">MB FREECONTACT EN</a> <a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

### IE-PI-HYB-10P

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26


D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Dimensioned drawing



## IE-PI-HYB-10P

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Hybrid

Hybrid, 10-pole. Inserts for plug-in connectors Variant 14



## General ordering data

Type	IE-PIC-HYB-S-0,75-300	Version
Order No.	<a href="#">1068950000</a>	Crimp contact, for plug insert, Hybrid
GTIN (EAN)	4032248823109	
Qty.	300 pc(s).	
Type	IE-PIC-HYB-S-0,2-300	Version
Order No.	<a href="#">1135150000</a>	Crimp contact, for plug insert, Hybrid
GTIN (EAN)	4032248915347	
Qty.	300 pc(s).	
Type	IE-PIC-HYB-S-0,5-300	Version
Order No.	<a href="#">1096180000</a>	Crimp contact, for plug insert, Hybrid
GTIN (EAN)	4032248869152	
Qty.	300 pc(s).	

## Crimping tools



## Crimping tools for Weidmüller contacts for RSV and DSTV-HD systems

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

## General ordering data

Type	HTF HYB	Version
Order No.	<a href="#">1119580000</a>	Pressing tool, Crimping tool for contacts, 0.08mm², 1mm²,
GTIN (EAN)	4032248900626	FoderBcrimp
Qty.	1 pc(s).	