

IE-BSS-V14M-HYB-10P-FJ**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

PushPull plug-in connector set according to IEC
61076-3-117 ver.14 (PROFINET), metal incl. hybrid insert

General ordering data

Version	Hybrid flange, IP67, Cat.5 (ISO/IEC 11801)
Order No.	1072900000
Type	IE-BSS-V14M-HYB-10P-FJ
GTIN (EAN)	4032248831111
Qty.	10 pc(s).

IE-BSS-V14M-HYB-10P-FJ

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	55.47 g
------------	---------

Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

General data

Category	Cat.5 (ISO/IEC 11801)	Connection 1	Hybrid (Q10)
Connection 2	Crimp	Plugging cycles	500
Protection degree	IP67	Sheath diameter, max.	10 mm
Sheath diameter, min.	5 mm	Shielding	360°; all-round enclosure
Type of mounting	2 screws	Wire connection cross section, finely stranded, max.	0.75 mm ²
Wire connection cross section, finely stranded, min.	0.08 mm ²	Wire cross-section, finely stranded, max. (AWG)	AWG 20
Wire cross-section, finely stranded, min. (AWG)	AWG 27		

Electrical properties

Rated current	3 A per contact	Volume resistance	<10 mΩ
---------------	-----------------	-------------------	--------

General standards

Certificate no. (cULus)	E316369	Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14
-------------------------	---------	--------------------	--

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ETIM 9.0	EC001121
ECLASS 9.0	27-44-03-90	ECLASS 9.1	27-44-09-90
ECLASS 10.0	27-44-03-90	ECLASS 11.0	27-44-03-90
ECLASS 12.0	27-44-03-90	ECLASS 13.0	27-44-03-90

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E316369

IE-BSS-V14M-HYB-10P-FJ

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	PROFINET Manufacturer's Declaration
Engineering Data	CAD data – STEP
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN Manual Designation key / Type key
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN


IE-BSS-V14M-HYB-10P-FJ

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Installation cut-out



IE-BSS-V14M-HYB-10P-FJ**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Hybrid**

Hybrid, 10-pole. Inserts for plug-in connectors Variant 14

**General ordering data**

Type	IE-BIC-HYB-P-0,75-300	Version
Order No.	1068970000	Crimp contact, for flange insert, Hybrid
GTIN (EAN)	4032248823956	
Qty.	300 pc(s).	
Type	IE-BIC-HYB-P-0,2-300	Version
Order No.	1135160000	Crimp contact, for flange insert, Hybrid
GTIN (EAN)	4032248915477	
Qty.	300 pc(s).	
Type	IE-BIC-HYB-P-0,5-300	Version
Order No.	1096150000	Crimp contact, for flange insert, Hybrid
GTIN (EAN)	4032248869114	
Qty.	300 pc(s).	

Dust caps

For protecting your devices against dust and dirt.

**General ordering data**

Type	IE-BP-V14P	Version
Order No.	1058310000	Flange-mounted housing, protective cap
GTIN (EAN)	4032248799404	
Qty.	10 pc(s).	

IE-BSS-V14M-HYB-10P-FJ

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Crimping tools****Crimping tools for Weidmüller contacts for RSV and DSTV-HD systems**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

General ordering data

Type	HTF HYB	Version
Order No.	1119580000	Pressing tool, Crimping tool for contacts, 0.08mm ² , 1mm ² ,
GTIN (EAN)	4032248900626	FoderBcrimp
Qty.	1 pc(s).	

Hybrid cable

Bulk stock, copper cable, hybrid, flexible, 6 x 0.5 mm² + 4 x AWG 22/7

General ordering data

Type	IE-C5DHAG-MW	Version
Order No.	1172250000	Connecting line, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC,
GTIN (EAN)	4032248964543	Products sold by meter, from 110 m
Qty.	110 m	