

KSWF M16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	KSWF (flat gasket - vulcanised fibre), Sealing ring, M 16, Vulcanized fibre
Order No.	1076680000
Type	KSWF M16
GTIN (EAN)	4032248838615
Qty.	25 pc(s).

KSWF M16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	1.5 mm	Height (inches)	0.059 inch
Net weight	0.08 g		

Temperatures

Operating temperature	-40 °C...95 °C
-----------------------	----------------

General information

Cable glands	M 16	Diameter of sealing ring	25 mm
External thread	M 16	Internal thread	M 16
Material	Vulcanized fibre	Number of wires	1
Operating temperature range, max.	95 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Silicone	No

Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ETIM 9.0	EC001181
ECLASS 9.0	27-43-03-19	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-43-03-19	ECLASS 11.0	27-43-03-19
ECLASS 12.0	27-43-03-19	ECLASS 13.0	27-43-03-19

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

KSWF M16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

