

VKSW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Wire channel cutter for manual operation in cutting wiring channels and covers up to 125 mm wide and a wall thickness of 2.5 mm. Only for plastics not reinforced by fillers.

- Cutting with no burrs or waste
- Length stop (1,000 mm) with guide device for precise cutting to length
- Table-top unit for mounting on a workbench or similar work surface
- Hardened cutting edges made of special steel

Általános rendelési adatok

Verzió	Cable duct cutting device
Rendelési szám	1137530000
Típus	VKSW
GTIN (EAN)	4032248919406
Qty.	1 Stück

Műszaki adatok

Méretetek és tömegek

Mélység	290 mm	Mélység (coll)	11,417 inch
Magasság	285 mm	Magasság (coll)	11,22 inch
Szélesség	280 mm	Szélesség (coll)	11,024 inch
Nettó tömeg	305 g		

Vágószerzők

Cutting width max.	125 mm
--------------------	--------

Besorolások

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-50-03	ECLASS 9,1	21-01-90-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-04-50-03
ECLASS 12.0	21-04-50-03	ECLASS 13.0	21-04-50-03

Termékek környezetvédelmi megfelelése

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Letöltések

Katalógusok	Catalogues in PDF-format
Kiadványok	

Tartozékok

Tartozékok/cserealkatrészek



Wire channel cutter for manual operation in cutting wiring channels and covers up to 125 mm wide and a wall thickness of 2.5 mm. Only for plastics not reinforced by fillers.

- Cutting with no burrs or waste
- Length stop (1,000 mm) with guide device for precise cutting to length
- Table-top unit for mounting on a workbench or similar work surface
- Hardened cutting edges made of special steel

Általános rendelési adatok

Típus	ERME VKSW	Verzió
Rendelési szám	1251270000	Pót vágókés
GTIN (EAN)	4050118042436	
Qty.	1 Stück	
Típus	SCHUTZPROFIL VKSW	
Rendelési szám	8007400000	
GTIN (EAN)	4050118392548	
Qty.	1 Stück	