

AP MCZ1.5 GN 1670**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Open miniature housing in modular terminal format with five tension clamp connections. A transparent hinged top plate can be used for labelling and provides access to potentiometer and status displays. Plug-in cross-connectors can be used to interconnect the three top connections. A cover plate for closing off the housing is also available.

General ordering data

Version	Small housing, OMNIMATE Housing - TERMINAL-BOX green, End plate, Width: 1.5 mm
Order No.	1161290000
Type	AP MCZ1.5 GN 1670
GTIN (EAN)	4032248950355
Qty.	50 pc(s).

AP MCZ1.5 GN 1670**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	55.85 mm	Height (inches)	2.199 inch
Width	1.5 mm	Width (inches)	0.059 inch
Length	91 mm	Length (inches)	3.583 inch
Net weight	5.972 g		

Material data

Comparative Tracking Index (CTI)	600 ≤ CTI	Insulating material group	I
UL 94 flammability rating	V-0		

General data

Colour	green	Colour chart (similar)	RAL 6032
Encapsulation option	Yes	Protection degree	IP20, IP20 in installed state

Classifications

ETIM 7.0	EC000886	ETIM 8.0	EC000886
ETIM 9.0	EC001031	ECLASS 11.0	27-14-11-33
ECLASS 12.0	27-14-11-33	ECLASS 13.0	27-19-06-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL ANALO.SIGN.CONV. EN MB DEVICE MANUF. EN FL MACHINE SAFETY EN FL 72H SAMPLE SER EN PO OMNIMATE EN

AP MCZ1.5 GN 1670

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

