

**MTA 45 MF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Mounting accessory for Weidmüller Power Supplys.

**General ordering data**

|            |                                       |
|------------|---------------------------------------|
| Version    | Electronics housings, Mounting flange |
| Order No.  | <a href="#">1251310000</a>            |
| Type       | MTA 45 MF                             |
| GTIN (EAN) | 4050118042719                         |
| Qty.       | 1 pc(s).                              |

**MTA 45 MF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Height     | 10.5 mm | Height (inches) | 0.413 inch |
| Width      | 47 mm   | Width (inches)  | 1.85 inch  |
| Length     | 97.3 mm | Length (inches) | 3.831 inch |
| Net weight | 97 g    |                 |            |

**General data**

|                   |      |        |      |
|-------------------|------|--------|------|
| Protection degree | IP20 | Weight | 97 g |
|-------------------|------|--------|------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002625    | ETIM 7.0    | EC002625    |
| ETIM 8.0    | EC002625    | ETIM 9.0    | EC002625    |
| ECLASS 9.0  | 27-18-28-07 | ECLASS 9.1  | 27-04-92-90 |
| ECLASS 10.0 | 27-18-28-07 | ECLASS 11.0 | 27-18-28-07 |
| ECLASS 12.0 | 27-18-28-07 | ECLASS 13.0 | 27-18-28-07 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |