

THM WO VIN 25/25 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 3.2 - 4.8 mm, 25 x 25 mm, white
Order No.	1253150000
Type	THM WO VIN 25/25 WS
GTIN (EAN)	4050118045673
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

THM WO VIN 25/25 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.065 mm	Depth (inches)	0.003 inch
Height	25 mm	Height (inches)	0.984 inch
Width	25 mm	Width (inches)	0.984 inch
Net weight	743 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

General data

Adhesive	Polyacrylate adhesive		
Approval acc. to UL 969	No		
Colour	white		
Halogen	Yes		
Material	Vinyl film		
Material colour according to resistance code	9		
Number of markers per combination	1 Label reel = Conductor and cable markers		
Number of markers per packaging unit	Form of supply	Label reel	
Number per roll	5,000		
Operating temperature range	-40...80 °C		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-40 °C		
Size of labelling field	10 x 25 mm		
Type of printing	neutral		
UL 94 flammability rating	V-0		
Version	Self-adhesive		
Width	25 mm		

Conductor and cable markers

Conductor O.D.	3.2 - 4.8 mm	Conductor O.D., max.	4.8 mm
Conductor O.D., min.	3.2 mm	Conductor cross-section, max.	120 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 120 mm ²
Halogen	Yes		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

THM WO VIN 25/25 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

