

ETA 1180 01 0.7A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Weidmueller offer circuit breakers for the integration of our fuse terminals for automotive fuses with a range from 100 mA to 25 A.

General ordering data

Version	Miniature fuse, 0.7 A
Order No.	1278930000
Type	ETA 1180 01 0.7A
GTIN (EAN)	4050118091519
Qty.	5 pc(s).

ETA 1180 01 0.7A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	52.3 mm	Depth (inches)	2.059 inch
Height	24.4 mm	Height (inches)	0.961 inch
Width	8.2 mm	Width (inches)	0.323 inch
Net weight	10.6 g		

Material data

Colour	black
--------	-------

System specifications

Version	Fuse cartridge
---------	----------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

Fuse cartridges

Colour	black	Current	0.7 A
Version	Fuse cartridge		

General

Installation advice	Direct mounting
---------------------	-----------------

Rating data

Rated voltage	64 V	Rated current	0.7 A
---------------	------	---------------	-------

Classifications

ETIM 6.0	EC000035	ETIM 7.0	EC000035
ETIM 8.0	EC002704	ETIM 9.0	EC002704
ECLASS 9.0	27-14-20-01	ECLASS 9.1	27-14-20-01
ECLASS 10.0	27-14-20-01	ECLASS 11.0	27-14-20-01
ECLASS 12.0	27-14-20-01	ECLASS 13.0	27-14-20-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format