

CBH 8.1/6.2 NC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Fastening of cables or bundles with ties into electrical switchgears and cabinets.

General ordering data

Version	Cable ties, 6.2 x 8.1 mm, Plastic, 80 N
Order No.	1279200000
Type	CBH 8.1/6.2 NC
GTIN (EAN)	4008190068820
Qty.	100 pc(s).

CBH 8.1/6.2 NC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	2 mm	Depth (inches)	0.079 inch
Height	8.1 mm	Height (inches)	0.319 inch
Width	6.2 mm	Width (inches)	0.244 inch
Net weight	1.02 g		

Temperatures

Operating temperature range	-40...105 °C
-----------------------------	--------------

Installation materials

Diameter of fastening hole	6.5 mm	For re-opening	No
Halogen	No	Material	Plastic
Max. cable tie width	7.8 mm	Operating temperature range, max.	105 °C
Operating temperature range, min.	-40 °C	Tensile strength	80 N
Tensile strength (Pound-force)	18 lbf	UL 94 flammability rating	V-2
UV-resistant	Yes	Version	for mounting plate

Classifications

ETIM 6.0	EC000449	ETIM 7.0	EC000449
ETIM 8.0	EC000449	ETIM 9.0	EC000449
ECLASS 9.0	23-15-90-07	ECLASS 9.1	27-40-07-90
ECLASS 10.0	27-40-07-90	ECLASS 11.0	23-15-25-09
ECLASS 12.0	23-15-25-09	ECLASS 13.0	23-15-25-09

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

CBH 8.1/6.2 NC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing

