

KTB GP 765015 CD S4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

General ordering data

Version	Klippon TB (Terminal Box), flange plate, straight, Height: 345 mm, Width: 117 mm, Depth: 3 mm, Gland plates: left, right, Material: Stainless steel 1.4404, electropolished, silver
Order No.	1281240000
Type	KTB GP 765015 CD S4
GTIN (EAN)	4050118071894
Qty.	1 pc(s).

KTB GP 765015 CD S4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	3 mm	Depth (inches)	0.118 inch
Height	345 mm	Height (inches)	13.583 inch
Width	117 mm	Width (inches)	4.606 inch
Net weight	825 g		

General information

Gland plates	left, right	Integral fixing	Screwed
Material	Stainless steel 1.4404	Material thickness	3 mm
Protection class (UL)	Type 3, Type 4X, Type 12	Surface finish	electropolished

General information on accessories

Material	Stainless steel 1.4404	Material thickness	3 mm
Surface finish	electropolished		

Classifications

ETIM 6.0	EC000211	ETIM 7.0	EC000211
ETIM 8.0	EC000211	ETIM 9.0	EC000211
ECLASS 9.0	27-14-24-21	ECLASS 9.1	27-18-92-90
ECLASS 10.0	27-14-24-21	ECLASS 11.0	27-14-24-21
ECLASS 12.0	27-14-24-21	ECLASS 13.0	27-14-24-21

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--