

IE-SW-VL08T-6GT-2GS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

- Wide ranges of variations with 5 to 16 ports
- Variations for Gigabit Ethernet
- Two redundant power inputs 12/24/48 V DC
- Models with copper and fibre-optic interface (multi-mode and singlemode)
- Extensive approvals: CE, FCC, cULus, Class I Div. 2 / ATEX Zone 2, DNV-GL

General ordering data

Version	Network switch, unmanaged, Gigabit Ethernet, Number of ports: 6 * RJ45 10/100/1000BaseT(X), 2 * combo-ports (10/100/1000BaseT(X) or 100/1000BaseSFP), IP30, -40 °C...75 °C
Order No.	1286870000
Type	IE-SW-VL08T-6GT-2GS
GTIN (EAN)	4050118077759
Qty.	1 pc(s).

Creation date April 29, 2024 2:36:34 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

IE-SW-VL08T-6GT-2GS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	105 mm	Depth (inches)	4.134 inch
Height	135 mm	Height (inches)	5.315 inch
Width	52.85 mm	Width (inches)	2.081 inch
Net weight	630 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...75 °C
Humidity	5 to 95 % (non-condensing)		

EMC conformity and approvals

EMC standards	EN 55032, EN 55035, EN 61000-6-4, EN 61000-6-2, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 Ghz: 10 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 2 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 2 kV, IEC 61000-4-6 CS: 10 V, IEC 61000-4-8	Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex ec nC IIC T4 Gc, EN IEC 60079-0, EN IEC 60079-15, EN IEC 60079-7
Free fall	According to IEC 60068-2-32	Safety standard	UL508, EN 60950-1
Ship use	DNV	Shock	according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	75 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Guarantee

Time interval	5 years
---------------	---------

IE-SW-VL08T-6GT-2GS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Interfaces

Alarm contact	1 relay output with a current capacity of 1 A at 24 V DC	Fibre-optic ports	100/1000Base SFP Slot
Function DIP switch	Port surveillance, Broadcast storm protection enable/disable, Enable/disable jumbo frame support, Activate/deactivate IEEE 802.3az energy-efficient Ethernet	LED indicator	Power LED: PWR1, PWR2, FAULT, 10/100/1000M (TP-Port), 100/1000M (SFP-Port)
Note	The SFP slot can only be used with Weidmüller SFP transceivers belonging to product group "SFP transceivers for use with switches of Basic-, Value- and PremiumLine". Third-party SFP transceivers are not accepted by the switch.	Number of ports	6 * RJ45 10/100/1000BaseT(X), 2 * combo-ports (10/100/1000BaseT(X) or 100/1000BaseSFP)
RJ45 ports	10/100/1000BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port		

MTBF

MTBF	According to Standard	Telcordia (Bellcore), GB
	Operating time (hours), min.	2,260,195 h

Power supply

Connection type	1 removable 6-pin terminal block		
Current consumption	0.34 A at 24 V		
Reverse polarity protection	Available		
Voltage supply	12/24/48 V DC, 2 redundant inputs		
Voltage supply range	Voltage type	DC	
	Voltage, min.	9.6 V	
	Voltage, max.	60 V	

Switch characteristics

Bandwidth backplane	16 Gbit/s	Jumbo frame support	up to 9.6 KB
MAC table size	8 K	Packet buffer size	4,000 Kbit

Technical data

Housing main material	Metal	Protection degree	IP30
Speed	Gigabit Ethernet	Switch	unmanaged
Type of mounting	DIN rail		

IE-SW-VL08T-6GT-2GS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X) and 100BaseFX, IEEE 802.3ab for 1000BaseT(X), IEEE 802.3z for 1000BaseX, IEEE 802.3x for flow con- trol, IEEE 802.3az Ener- gy-Efficient Ethernet		

Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
ETIM 8.0	EC000734	ETIM 9.0	EC000734
ECLASS 9.0	19-17-01-06	ECLASS 9.1	19-17-01-06
ECLASS 10.0	19-17-04-02	ECLASS 11.0	19-17-04-02
ECLASS 12.0	19-17-04-02	ECLASS 13.0	19-17-04-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197
Certificate no. (cULusEX)	E223527

Downloads

Approval/Certificate/Document of Con- formity	CC-Link IE Field Certificate DNV certificate ATEX certificate EU Declaration of Conformity UK Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Hardware Installation Guide
Catalogues	Catalogues in PDF-format
Brochures	

IE-SW-VL08T-6GT-2GS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Mounting kit for 19" rack assembly

- For assembling DIN rail-based devices on 19" racks



General ordering data

Type	RM-KIT	Version
Order No.	1241440000	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 pc(s).	

SFP transceiver (for use with switches of Basic-, Value- and PremiumLine)



- Supports DDM (Digital Diagnostic Monitoring)
- IEEE 802.3z compliant (Gigabit Ethernet SFPs)
- IEEE 802.3u compliant (Fast Ethernet SFPs)
- Symmetric LVPECL I/Os (Gigabit Ethernet SFPs)
- Symmetric PECL I/Os (Fast Ethernet SFPs)
- TTL signal detection indicator
- Pluggable in operation (hot pluggable)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Basic-, Value- and PremiumLine

General ordering data

Type	IE-SFP-1GLXLC	Version
Order No.	1241510000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 10 km, 0 °C...60 °C
GTIN (EAN)	4050118029338	
Qty.	1 pc(s).	
Type	IE-SFP-1GLXLC-T	Version
Order No.	1286720000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 10 km, -40 °C...85 °C
GTIN (EAN)	4050118077537	
Qty.	1 pc(s).	
Type	IE-SFP-1FELLC-T	Version
Order No.	1241480000	SFP Transceiver, 100 Mbps, Singlemode, LC-Duplex, 80 km, -40 °C...85 °C
GTIN (EAN)	4050118029178	
Qty.	1 pc(s).	
Type	IE-SFP-1FESLC-T	Version
Order No.	1241470000	SFP Transceiver, 100 Mbps, Singlemode, LC-Duplex, 40 km, -40 °C...85 °C
GTIN (EAN)	4050118029420	
Qty.	1 pc(s).	
Type	IE-SFP-1GLSXC	Version
Order No.	1241500000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 2 km, 0 °C...60 °C
GTIN (EAN)	4050118029314	
Qty.	1 pc(s).	

IE-SW-VL08T-6GT-2GS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	IE-SFP-1FEMLC-T	Version
Order No.	1241450000	SFP Transceiver, 100 Mbps, Multimode, LC-Duplex, 4 km, -40 °C...85 °C
GTIN (EAN)	4050118029192	
Qty.	1 pc(s).	
Type	IE-SFP-1GSXLC	Version
Order No.	1241490000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 0.55 km, 0 °C...60 °C
GTIN (EAN)	4050118029512	
Qty.	1 pc(s).	
Type	IE-SFP-1GLHXL	Version
Order No.	1241520000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 40 km, 0 °C...60 °C
GTIN (EAN)	4050118029369	
Qty.	1 pc(s).	
Type	IE-SFP-1GLSXLC-T	Version
Order No.	1286710000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 2 km, -40 °C...85 °C
GTIN (EAN)	4050118077520	
Qty.	1 pc(s).	
Type	IE-SFP-1GSXLC-T	Version
Order No.	1286700000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 0.55 km, -40 °C...85 °C
GTIN (EAN)	4050118077261	
Qty.	1 pc(s).	
Type	IE-SFP-1GLHXL-T	Version
Order No.	1286730000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 40 km, -40 °C...85 °C
GTIN (EAN)	4050118077728	
Qty.	1 pc(s).	

Discontinued products

General ordering data

Type	IE-SFP-1G20ALC-T
Order No.	1286760000
GTIN (EAN)	4050118077278
Qty.	1 pc(s).
Type	IE-SFP-1G10BLC
Order No.	1241540000
GTIN (EAN)	4050118029376
Qty.	1 pc(s).
Type	IE-SFP-1G10ALC
Order No.	1241530000
GTIN (EAN)	4050118029406
Qty.	1 pc(s).

IE-SW-VL08T-6GT-2GS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

Type	IE-SFP-1G20BLC-T
Order No.	1286770000
GTIN (EAN)	4050118077513
Qty.	1 pc(s).

Type	IE-SFP-1G10ALC-T
Order No.	1286740000
GTIN (EAN)	4050118077735
Qty.	1 pc(s).

Type	IE-SFP-1G10BLC-T
Order No.	1286750000
GTIN (EAN)	4050118077544
Qty.	1 pc(s).

Type	IE-SFP-1G20ALC
Order No.	1241550000
GTIN (EAN)	4050118029505
Qty.	1 pc(s).

Type	IE-SFP-1G20BLC
Order No.	1241570000
GTIN (EAN)	4050118029383
Qty.	1 pc(s).