

SAISW-5/11-7/8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female sockets for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The 7/8" round plug-in connectors can transmit large amount of power.

The screw connection can be used in a wide range of applications. With this technology the conductor, optionally with wire-end ferrules, can be plugged into connection elements and secured with a screw. It is the classic, cheapest form of connection technology that also supports multi-conductor connections.

General ordering data

Version	Field attachable connector, 7/8", pin, 90°
Order No.	1291990000
Type	SAISW-5/11-7/8
GTIN (EAN)	4050118086898
Qty.	1 pc(s).

SAISW-5/11-7/8

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	63 g
------------	------

Technical data customisable plug-in connectors

Cable diameter, max.	10 mm	Cable diameter, min.	8 mm
Cable glands	PG 11	Coding	none
Conductor cross-section, max.	1.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Connection cross-section, max.	1.5 mm ²	Connection cross-section, min.	0.14 mm ²
Contact material	CuZn	Contact surface	Gold-plated
Housing main material	PBT	Insulation strength	10 ⁸ Ω
Number of poles	5	Plugging cycles	≥ 50
Pollution severity	3	Protection degree	IP67
Rated current	9 A	Rated current	9 A (4- and 5-pole), 12 A (3-pole)
Rated voltage	300 V	Shield connection	No
Temperature range of housing	-40 ... +85 °C	Threaded ring material	Diecast zinc
Type of connection	Screw connection		

General data

Cable diameter, max.	10 mm	Cable diameter, min.	8 mm
Cable glands	PG 11	Coding	none
Conductor O.D.	-	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.5 mm ²	Connection thread	7/8"
Contact material	CuZn	Contact surface	Gold-plated
Housing main material	PBT	Insulation strength	10 ⁸ Ω
Number of poles	5	Plugging cycles	≥ 50
Pollution severity	3	Protection degree	IP67
Rated current	9 A	Rated current	9 A (4- and 5-pole), 12 A (3-pole)
Rated impulse voltage	4,000 V	Rated voltage	300 V
Rated voltage	300 V	Rated voltage (UL)	600 V
Shield connection	No	Temperature range of housing	-40 ... +85 °C
Type of connection	Screw connection		

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	7baf363e-d867-435e-844e-c01f32ebf146

SAISW-5/11-7/8

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E307231

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

SAISW-5/11-7/8

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

