

**PAC-UNIV-HE14-F-3M5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

**General ordering data**

Version	Pre-assembled cable, PAC
Order No.	<a href="#">1349740035</a>
Type	PAC-UNIV-HE14-F-3M5
GTIN (EAN)	4099986579484
Qty.	1 pc(s).

## PAC-UNIV-HE14-F-3M5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	248 g
------------	-------

## Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50 °C
---------------------	-------------	-----------------------	-------------

## General Data

Cable	Cable LiYY	Cable length	3.5 m
Connector PLC side	H0.14/10 (FERRULES 0.14mm <sup>2</sup> )	Interface connector	FLAT CABLE CONECTOR HE10 14P
Material	PVC	Number of poles, min.	14-pole
Outer diameter	7,6 ± 1 mm	Suitable for	Digital signals
Wire cross-section	0.14 mm <sup>2</sup>		

## Electrical Data

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
Operating voltage	≤ 60 V DC ≤ 25 V AC	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 V DC ≤ 25 V AC	Resistance	≤ 150 mΩ/m
Total current, max.	3 A		

## Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ETIM 9.0	EC000237
ECLASS 9.0	27-24-22-20	ECLASS 9.1	27-24-22-20
ECLASS 10.0	27-24-22-20	ECLASS 11.0	27-24-22-20
ECLASS 12.0	27-24-22-20	ECLASS 13.0	27-24-22-20

## Approvals

ROHS	Conform
------	---------

## Downloads

User Documentation	<a href="#">Colours chart</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>