


**VPU III SO LD+A****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Type III surge protection**

Compact type III arrester for AC/DC protection acc. to IEC 61643-11:2012 and EN 61643-11. Suitable for protecting end devices. Installed in the vicinity of the equipment to be protected. The arrester can be used as a single-port arrester when nominal current is greater than 16 A.

**General ordering data**

Version	Surge voltage arrester, Low voltage, without telecomm. contact, Single-phase
Order No.	<a href="#">1351700000</a>
Type	VPU III SO LD+A
GTIN (EAN)	4050118158458
Qty.	1 pc(s).

## VPU III SO LD+A

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	25 mm	Depth (inches)	0.984 inch
Height	35 mm	Height (inches)	1.378 inch
Width	12 mm	Width (inches)	0.472 inch
Net weight	34 g		

## Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-25 °C...55 °C
Humidity	5 - 95% rel. humidity		

## Connection data, remote alert

Connection type	Miscellaneous	Cross-section for connected wire, solid core, max.	1.5 mm <sup>2</sup>
-----------------	---------------	--	---------------------

## General data

Acoustic signal	Yes	Colour	black
Design	Flush mounting	Optical function display	Green LED = OK, Red LED = arrester is defective, replace
Protection degree	IP20	Segment	Power distribution
UL 94 flammability rating	V-0	Version	without telecomm. contact

## Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	II
--------------------	---	------------------------	----

## Rated data IEC / EN

Acoustic signal	Yes	Combined pulse U <sub>OC</sub>	3 kV
Energy coordination (≤10 m)	Type II, Type III	Fuse	16 A
Leakage current at U <sub>n</sub>	30 µA	Low voltage network	Single-phase
Mains frequency at 250 V <sub>max</sub>	50...60Hz	Max. continuous voltage, U <sub>c</sub> (AC)	275 V
Number of poles	1	PE conductor current I <sub>PE</sub>	10 µA
Protection level U <sub>p</sub> at I <sub>N</sub> (L/N-PE)	≤ 1.5 kV	Rated voltage (AC)	230 V
Requirements category acc. to IEC 61643-11	Type III	Requirements class, acc. to EN 61643-11	T3
Response time	< 100µs	Short-circuit current rating I <sub>SCCR</sub>	1.5 kA
Signalling contact	No	Standards	IEC61643-11, EN61643-11
Temporary surge voltage (over-voltage) - TOV	440 V	Voltage type	AC

## Connection data

Wire connection cross section, finely stranded, max.	1 mm <sup>2</sup>
--	-------------------

## Guarantee

Time interval	5 years
---------------	---------

## VPU III SO LD+A

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90

## Tender specification sheets

Long specification	Surge protection according to the requirements of Class III in accordance with IEC 61643-11, EN61643-11:2013. The arrester serves as surge protection and is used in applications in accordance with IEC 61643-12. The arrester is installed in the vicinity of the equipment that needs protection in a standard installation/distributor housing. The VPU III SO LD +A is earthed between the phase and the neutral conductor. With thermal separation device on the varistor. If there is no longer any protection, the red LED goes out and an acoustic signal sounds. Rated voltage: 230 VAC In/max (8/20 µs): 1.5 kA protection level < 1.5 kV Type: Weidmüller VPU III R SO LD A Order No. 1351700000 or equivalent	Short specification	Class III arrester with Uoc: 3 kV suitable for 230 V AC mains systems. Protection level < 1.5 kV. With red LED display and acoustic alert Type: Weidmüller VPU III SO LD A Order no. 1351700000 or equivalent
--------------------	---	---------------------	---

## Approvals

Approvals



ROHS

Conform

## Downloads

Approval/Certificate/Document of Conformity

[EU Konformitätserklärung / EU Declaration of Conformity](#)

User Documentation

[Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

## VPU III SO LD+A

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Electric symbol

