

IE-CD-VAPM24V-C-MA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



View from below

Y-distributor / connection coupling, FreeCon for plug-in
PushPull Power connector to PROFINET specification,
metal

General ordering data

Version	Coupling, FreeCon, Supply, IP65, If thread-locking fluid is used
Order No.	1397690000
Type	IE-CD-VAPM24V-C-MA
GTIN (EAN)	4050118198669
Qty.	1 pc(s).

IE-CD-VAPM24V-C-MA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	425.36 g
------------	----------

Temperatures

Operating temperature	-40 °C...70 °C
-----------------------	----------------

Classifications

ETIM 6.0	EC001264	ETIM 7.0	EC001264
ETIM 8.0	EC001264	ETIM 9.0	EC001264
ECLASS 9.0	19-17-01-23	ECLASS 9.1	19-17-01-25
ECLASS 10.0	19-17-01-23	ECLASS 11.0	19-17-01-23
ECLASS 12.0	19-17-01-23	ECLASS 13.0	19-17-01-23

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E316369

Downloads

Approval/Certificate/Document of Conformity	PROFINET Manufacturer's Declaration
Engineering Data	CAD data – STEP
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	MB FREECONTACT EN FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN


IE-CD-VAPM24V-C-MA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings


Dimensioned drawing



Dimensioned drawing



Dimensioned drawing



Dimensioned drawing

