

**HDC HP 250 F CM3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

Version	HDC insert, Female, Crimp connection
Order No.	<a href="#">1415420000</a>
Type	HDC HP 250 F CM3
GTIN (EAN)	4050118216387
Qty.	1 pc(s).

**HDC HP 250 F CM3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	40 g
------------	------

**General data**

Colour	black	Free from halogens	false
Material	Copper alloy	Type	Female
Type of connection	Crimp connection		

**Version**

Material	Copper alloy	Type of connection	Crimp connection
----------	--------------	--------------------	------------------

**Classifications**

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ETIM 9.0	EC000796
ECLASS 9.0	27-44-02-04	ECLASS 9.1	27-44-02-04
ECLASS 10.0	27-44-02-04	ECLASS 11.0	27-44-02-04
ECLASS 12.0	27-44-02-04	ECLASS 13.0	27-44-02-04

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">1487780000_00_11_13_BPZ_HDC_HP250-550_web.pdf</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>

## HDC HP 250 F CM3

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Crimp contacts CM3



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

## General ordering data

Type	HDC-C-M3-BM10.0AG	Version
Order No.	<a href="#">1682310000</a>	Heavy-duty connectors, Crimp contact, CM 3, Female, Conductor
GTIN (EAN)	4008190474041	cross-section, max.: 10, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M3-BM4.0AG	Version
Order No.	<a href="#">1682270000</a>	Heavy-duty connectors, Crimp contact, CM 3, Female, Conductor
GTIN (EAN)	4008190474003	cross-section, max.: 4, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M3-BM1.5AG	Version
Order No.	<a href="#">1698130000</a>	Heavy-duty connectors, Crimp contact, CM 3, Female, Conductor
GTIN (EAN)	4008190885045	cross-section, max.: 1.5, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M3-BM2.5AG	Version
Order No.	<a href="#">1698150000</a>	Heavy-duty connectors, Crimp contact, CM 3, Female, Conductor
GTIN (EAN)	4008190885069	cross-section, max.: 2.5, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M3-BM6.0AG	Version
Order No.	<a href="#">1682290000</a>	Heavy-duty connectors, Crimp contact, CM 3, Female, Conductor
GTIN (EAN)	4008190474027	cross-section, max.: 6, turned, Copper alloy
Qty.	100 pc(s).	