

HSS-HF 1.6-3.2 EL W13M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

| | |
|--------------------|---|
| Version | Conductor and cable markers, 1.6 - 3.2 mm, white |
| Order No. | 1423340000 |
| Type | HSS-HF 1.6-3.2 EL W13M |
| GTIN (EAN) | 4050118227581 |
| Qty. | 1 pc(s). |
| compatible printer | 2599430000 2599440000 |

HSS-HF 1.6-3.2 EL W13M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|-----------|-----------------|-------------|
| Depth | 0.7 mm | Depth (inches) | 0.028 inch |
| Width | 5.6 mm | Width (inches) | 0.22 inch |
| Length | 13,000 mm | Length (inches) | 511.81 inch |
| Net weight | 110 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -55...105 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|-----------|-----------------------------------|--------------|
| Colour | white | Halogen | No |
| Length | 13,000 mm | Material | Polyolefine |
| Number per roll | 1 | Operating temperature range | -55...105 °C |
| Operating temperature range, max. | 105 °C | Operating temperature range, min. | -55 °C |
| Printed characters | without | Type of printing | neutral |
| Width | 5.6 mm | | |

Conductor and cable markers

| | | | |
|-----------------------------------|---------------------|----------------------------------|---------------------------|
| Conductor O.D. | 1.6 - 3.2 mm | Conductor O.D., max. | 3.2 mm |
| Conductor O.D., min. | 1.6 mm | Conductor cross-section, max. | 1.5 mm ² |
| Conductor cross-section, min. | 0.5 mm ² | Cross-section for connected wire | 0.5 - 1.5 mm ² |
| Halogen | No | Rate of shrinkage | 2:1 |
| Recommended shrinking temperature | 90 °C | Text field height | 5.4 mm |
| Text field width | 0 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | NFX 70-100-1 2006 + NF X 70-100-2 2006 BS EN ISO 4589-2 1999 EN 45545-2:2020 |
| Catalogues | Catalogues in PDF-format |

HSS-HF 1.6-3.2 EL W13M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



HSS-HF 1.6-3.2 EL W13M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****THM MULTIMARK**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | |
|------------|----------------------------|
| Type | THM MMP ROLLER 30 |
| Order No. | 1357430000 |
| GTIN (EAN) | 4050118160253 |
| Qty. | 1 pc(s). |

| | |
|------------|----------------------------|
| Type | THM MMP ROLLER 115 |
| Order No. | 1357420000 |
| GTIN (EAN) | 4050118160314 |
| Qty. | 1 pc(s). |

Ink ribbons

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | |
|------------|-----------------------------|------------|
| Type | RIBBON HSS HF EL 40/300 ... | Version |
| Order No. | 1426210000 | Ink ribbon |
| GTIN (EAN) | 4050118228823 | |
| Qty. | 1 pc(s). | |

HSS-HF 1.6-3.2 EL W13M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | |
|------------|----------------------------|
| Type | MM PLUS ROLLER 110 |
| Order No. | 2672590000 |
| GTIN (EAN) | 4050118708097 |
| Qty. | 1 pc(s). |