

THM UR20 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM ET S7 non-adhesive, roll-packaged labels are used to label the SIMATIC ET 200S and S7-modules from Siemens.

The M-Print® PRO software can be used to individually print the THM ET S7 labels with a THM printer. Labels can be easily separated. The THM MultiMark printer ensures highly-resistant printing.

General ordering data

| | |
|--------------------|---|
| Version | THM, Insert markers, 90 x 8 mm, yellow |
| Order No. | 1429910000 |
| Type | THM UR20 GE |
| GTIN (EAN) | 4050118234787 |
| Qty. | 1 pc(s). |
| compatible printer | 2599430000 2599440000 |

THM UR20 GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.08 mm | Depth (inches) | 0.003 inch |
| Height | 90 mm | Height (inches) | 3.543 inch |
| Width | 8 mm | Width (inches) | 0.315 inch |
| Net weight | 327 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...80 °C |
|-----------------------------|-------------|

General data

| | | |
|--------------------------------------|-------------------------------|------------|
| Approval acc. to UL 969 | No | |
| Colour | yellow | |
| Halogen | Yes | |
| Material | Vinyl film | |
| Number of markers per combination | 1 Label reel = Insert markers | |
| Number of markers per packaging unit | Form of supply | Label reel |
| Number per roll | 1,000 | |
| Number per sheet | 1,000 | |
| Operating temperature range | -40...80 °C | |
| Operating temperature range, max. | 80 °C | |
| Operating temperature range, min. | -40 °C | |
| Printing method | Thermal transfer | |
| UL 94 flammability rating | HB | |
| Width | 8 mm | |

Device markers

| | |
|---------|-----|
| Halogen | Yes |
|---------|-----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ECLASS 9.0 | 27-40-06-29 | ECLASS 9.1 | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

THM UR20 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



THM UR20 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | |
|------------|----------------------------|------------|
| Type | RIBBON MM 110/360 SW | Version |
| Order No. | 2005070000 | Ink ribbon |
| GTIN (EAN) | 4050118390049 | |
| Qty. | 1 pc(s). | |