


**IE-FCI-D25-FM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

**General ordering data**

Version	FrontCom, Signal insert D-Sub, 25-pole, Socket / plug
Order No.	<a href="#">1450890000</a>
Type	IE-FCI-D25-FM
GTIN (EAN)	4050118255652
Qty.	1 pc(s).

## IE-FCI-D25-FM

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	17.9 mm	Height (inches)	0.705 inch
Width	12.5 mm	Width (inches)	0.492 inch
Length	53.1 mm	Length (inches)	2.091 inch
Net weight	17.389 g		

## Temperatures

Operating temperature	-55 °C...105
-----------------------	--------------

## Technical data

Contact resistance	≤ 20 mΩ	Contact surface	Gold-plated
Current-carrying capacity	3 A	Dielectric strength, contact / contact	1 kV <sub>eff</sub> / 1 min.
Housing main material	SPCC	Housing surface	tin-plated
Insulation strength	1000 MΩ at 500 V DC	Material insulator	PBT glass fibre reinforced UL 94 V-0
Number of poles	25		

## General data

Insert type	Signal insert D-Sub, 25-pole	Protection degree	IP20
-------------	------------------------------	-------------------	------

## Electrical properties

Contact resistance	≤ 20 mΩ	Dielectric strength, contact / contact	1 kV <sub>eff</sub> / 1 min.
Insulation strength	1000 MΩ at 500 V DC		

## General standards

Certificate No. (DNV)	TAA000022B	Certificate No. (UR)	E497345
-----------------------	------------	----------------------	---------

## Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ETIM 9.0	EC001121
ECLASS 9.0	27-44-03-90	ECLASS 9.1	27-18-90-90
ECLASS 10.0	27-44-03-90	ECLASS 11.0	27-44-03-90
ECLASS 12.0	27-18-28-92	ECLASS 13.0	27-18-28-92

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	14f36bdb-8bcd-4f24-8fb3-9538ad1abec6

## IE-FCI-D25-FM

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E497345

## Downloads


Approval/Certificate/Document of Conformity	<a href="#">GL_FrontCom</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">MB FREECONTACT EN</a> <a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

**IE-FCI-D25-FM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings****Dimensioned drawing****Dimensioned drawing**