

**GZ 10.0A/F****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

For protection against overcurrent, we offer cartridge fuse with dimensions 6.3x32 mm in sizes from 500 mA to 12.5 A.

**General ordering data**

|            |  |
|------------|--|
| Version    | Miniature fuse, quick-acting, 10 A, G-Si. 6.3 x 32 |
| Order No.  | <a href="#">1460640000</a>                         |
| Type       | GZ 10.0A/F   |
| GTIN (EAN) | 4050118266801                                      |
| Qty.       | 10 pc(s).  |

**GZ 10.0A/F****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 6.3 mm  | Depth (inches)  | 0.248 inch |
| Height     | 32 mm   | Height (inches) | 1.26 inch  |
| Width      | 6.3 mm  | Width (inches)  | 0.248 inch |
| Net weight | 2.476 g |                 |            |

**Material data**

|        |            |
|--------|------------|
| Colour | Light Grey |
|--------|------------|

**System specifications**

|         |                  |
|---------|------------------|
| Version | Fuse accessories |
|---------|------------------|

**Additional technical data**

|                     |                 |                  |         |
|---------------------|-----------------|------------------|---------|
| Installation advice | Direct mounting | Type of mounting | Plugged |
|---------------------|-----------------|------------------|---------|

**Fuse cartridges**

|                         |                      |                          |              |
|-------------------------|----------------------|--------------------------|--------------|
| Cartridge fuse          | G-Si. 6.3 x 32       | Characteristics          | quick-acting |
| Colour                  | Light Grey           | Current                  | 10 A         |
| Melting integral        | 240 A <sup>2</sup> s | Optical function display | No           |
| Power output (@ 1.5 In) | 4 W                  | Rated breaking capacity  | 1.5 kA       |
| Version                 | Fuse accessories     | Voltage drop             | 150 mV       |

**General**

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

**Rating data**

|               |       |               |      |
|---------------|-------|---------------|------|
| Rated voltage | 500 V | Rated current | 10 A |
|---------------|-------|---------------|------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000035    | ETIM 7.0    | EC000035    |
| ETIM 8.0    | EC002704    | ETIM 9.0    | EC002704    |
| ECLASS 9.0  | 27-14-20-01 | ECLASS 9.1  | 27-14-20-01 |
| ECLASS 10.0 | 27-14-20-01 | ECLASS 11.0 | 27-14-20-01 |
| ECLASS 12.0 | 27-14-20-01 | ECLASS 13.0 | 27-14-20-01 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |   |
|--------------------|---|
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |
| Brochures          |   |