

**H0,5/14 OR SP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

- supplied loose in poly-bag
- in multi-pack bag (5 x 100 pcs.)
- Linked of wire-end ferrule strips (50 pcs.)
- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

**General ordering data**

Version	Wire-end ferrule, Standard, 10 mm, 8 mm, orange
Order No.	<a href="#">1476230000</a>
Type	H0,5/14 OR SP
GTIN (EAN)	4050118283174
Qty.	100 pc(s).

## H0,5/14 OR SP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	0.018 g
------------	---------

## Technical data

Description of article	Wire end ferrule with plastic collar, orange	Version	Standard
------------------------	--	---------	----------

## Wire-end ferrules

Collar diameter (D2)	2.6 mm	Colour code	Weidmueller
Conductor cross-section	0.5 mm <sup>2</sup>	Contact surface diameter (D1)	1 mm
Contact surface length (L2)	8 mm	L1 in mm	14 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.2 mm
Stripping length	10 mm	Wire connection cross section AWG, max.	AWG 20

## Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E354986

## Downloads

User Documentation	<a href="#">Technical information - EN</a> <a href="#">Technical information - DE</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## H0,5/14 OR SP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Drawing

