

**KQI-M8/-6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Insulated cable connector in PVC or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

**General ordering data**

Version	cable lug, terminal end, Insulated cable connector, 6 mm <sup>2</sup> , 4 mm <sup>2</sup> - 6 mm <sup>2</sup>
Order No.	<a href="#">1492400000</a>
Type	KQI-M8/-6
GTIN (EAN)	4050118302257
Qty.	100 pc(s).

**KQI-M8/-6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	2.349 g
------------	---------

**Connectors**

Conductor cross-section	6 mm <sup>2</sup>	Conductor cross-section, max.	6 mm <sup>2</sup>
Conductor cross-section, min.	4 mm <sup>2</sup>	Connection length (l)	26 mm
Hole	M8	Identification colour	yellow
Inside diameter of collar (d4)	6.4 mm	Inside diameter of flange (d2)	8.4 mm
Inside diameter of shaft (d1)	3.6 mm	Insulation	Available
Material/plastic	PC	Outside diameter of shaft (d3)	14 mm

**Classifications**

ETIM 6.0	EC001059	ETIM 7.0	EC001059
ETIM 8.0	EC001059	ETIM 9.0	EC001059
ECLASS 9.0	27-40-02-12	ECLASS 9.1	27-40-02-12
ECLASS 10.0	27-40-02-12	ECLASS 11.0	27-40-02-12
ECLASS 12.0	27-40-02-12	ECLASS 13.0	27-40-02-12

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## KQI-M8/-6

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

