

KQI-M8/-16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Insulated cable connector in PVC or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 16 mm ² , 16 mm ² - 16 mm ²
Order No.	1492500000
Type	KQI-M8/-16
GTIN (EAN)	4050118302516
Qty.	50 pc(s).

KQI-M8/-16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	5.1 g
------------	-------

Connectors

Conductor cross-section	16 mm ²	Conductor cross-section, max.	16 mm ²
Conductor cross-section, min.	16 mm ²	Connection length (l)	33.5 mm
Hole	M8	Identification colour	blue
Inside diameter of collar (d4)	10.5 mm	Inside diameter of flange (d2)	8.4 mm
Inside diameter of shaft (d1)	5.8 mm	Insulation	Available
Material/plastic	PA	Outside diameter of shaft (d3)	14 mm

Classifications

ETIM 6.0	EC001059	ETIM 7.0	EC001059
ETIM 8.0	EC001059	ETIM 9.0	EC001059
ECLASS 9.0	27-40-02-12	ECLASS 9.1	27-40-02-12
ECLASS 10.0	27-40-02-12	ECLASS 11.0	27-40-02-12
ECLASS 12.0	27-40-02-12	ECLASS 13.0	27-40-02-12

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

KQI-M8/-16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

