

**KWN-M3/-0,75 90****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

Version	cable lug, terminal end, 0.5 mm <sup>2</sup> - 0.75 mm <sup>2</sup>
Order No.	<a href="#">1495180000</a>
Type	KWN-M3/-0,75 90
GTIN (EAN)	4050118304787
Qty.	100 pc(s).

**KWN-M3/-0,75 90****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	0.92 g
------------	--------

**Technical data**

Version	Euro series 90°
---------	-----------------

**Connectors**

Conductor cross-section, max.	0.75 mm <sup>2</sup>	Conductor cross-section, min.	0.5 mm <sup>2</sup>
Connection length (l)	7.5 mm	Flange width (b)	6.5 mm
Hole	M 3	Inside diameter of flange (d2)	3.2 mm
Inside diameter of shaft (d1)	1.4 mm	Insulation	not available
Outside diameter of shaft (d3)	3 mm	Shaft length (a)	5 mm

**Classifications**

ETIM 6.0	EC001051	ETIM 7.0	EC001051
ETIM 8.0	EC001051	ETIM 9.0	EC001051
ECLASS 9.0	27-40-02-05	ECLASS 9.1	27-40-02-05
ECLASS 10.0	27-40-02-05	ECLASS 11.0	27-40-02-05
ECLASS 12.0	27-40-02-05	ECLASS 13.0	27-40-02-05

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

Brochures
-----------

## KWN-M3/-0,75 90

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

