

CH20M45 S 2PSC/RUSC BK 2010**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Superior efficiency, flexibility and design - the "standard tailor-made fit"**

When selecting a housing design, flexibility is a key factor. Other important criteria are: scalability, customised design, innovative functionality and cost efficiency. You need a choice which offers the maximum performance with the minimum overhead.

The CH20M45 modular electronics housings come in an integrated extra-large assortment. It is suited for those electronics applications that require more space, such as compact controllers and power supplies.

The entire system is characterized by excellence: outstanding scalability and flexibility, a high security level, innovative application functionality and a variety of practical details.

- **Quicker installation** with features such as "Wire ready" the universal multi-tool screw head
- **User-friendly operations:** with clear and permanent labelling and extra marking possibilities, integrated release clip or transparent cover
- **Maximum interference immunity** with EMC-compliant construction featuring deeply overlapping module joint edges made from high-performance plastic
- **High operational reliability** with the unique Auto-Set coding system and featuring double-sided touch protection on the pin header and socket blocks

CH20M - a compact name for the most flexible system available on the market. It doesn't just stand for "Component Housing IP20 Modular".

CH20M also stands for efficiency and innovation throughout design, production and use.

General ordering data

| | |
|---------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version | Modular housing, OMNIMATE Housing - series CH20M black, Side element, RJ45 connection preparation, Side element, connection preparation mini-USB, Width: 45 mm |
| Order No. | 1500050000 |
| Type | CH20M45 S 2PSC/RUSC BK 2010 |
| GTIN (EAN) | 4050118308655 |
| Qty. | 6 pc(s). |
| Information regarding whole assembly, see referenced articles | 1104410000 |

CH20M45 S 2PSC/RUSC BK 2010**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|----------|-----------------|------------|
| Depth | 105.3 mm | Depth (inches) | 4.146 inch |
| Height | 22.8 mm | Height (inches) | 0.898 inch |
| Width | 45 mm | Width (inches) | 1.772 inch |
| Net weight | 14.7 g | | |

Temperatures

| | | | |
|-----------------------------|------------------|----------|---------------------------------------------------|
| Operating temperature range | -40 °C... 120 °C | Humidity | 5 - 93% rel. humidity, Tu = 40°C, no condensation |
|-----------------------------|------------------|----------|---------------------------------------------------|

Material data

| | | | |
|----------------------------------|-----------|---------------------------|-------------|
| Comparative Tracking Index (CTI) | 600 ≤ CTI | Insulating material | PA 66 GF 30 |
| Insulating material group | I | UL 94 flammability rating | V-0 |

General data

| | | | |
|----------------------|-------|------------------------|-------------------------|
| Colour | black | Colour chart (similar) | RAL 9011 |
| Encapsulation option | No | Protection degree | IP20 in installed state |

Component properties

| | | | |
|-------------------------------------------------------|-----|----------------------------------------------------|----------------|
| Cut out as preparation for functional port integrated | Yes | Number of connection levels | 2 |
| Number of poles, max. | 8 | Number of slots for female plugs | 2 |
| Number of ventilation openings | 2 | Type of cut out as preparation for functional port | Mini-USB, RJ45 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 7.0 | EC001031 | ETIM 8.0 | EC001031 |
| ETIM 9.0 | EC001031 | ECLASS 11.0 | 27-18-27-92 |
| ECLASS 12.0 | 27-18-27-92 | ECLASS 13.0 | 27-19-06-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|------------------------------------------|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |

CH20M45 S 2PSC/RUSC BK 2010

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings


Product image



Product image



Dimensioned drawing



CH20M45 S 2PSC/RUSC BK 2010

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

CH20M AD SHL 5.00/04 - Side element cover for CH20M22, CH20M45, CH20M67

**The perfect platform for function and innovation:**

Innovative function electronics require intelligent "packages" in order to integrate perfectly in the system environment.

The ongoing development and consistent expansion of the Weidmüller electronics housing portfolio provides a secure platform for future electronics applications whatever the design or intended use. CAD data for PCBs is provided for all enclosures. Screw and tension clamp terminals are available for all connections.

The consistent synergy between design, connection system and functionality lays the perfect foundation stone for electronics systems designed in line with market and application requirements.

Function, shape and manufacturing quality combine into a single logical unit that provides maximum reliability and operating comfort for the user.

General ordering data

| | | |
|------------|-----------------------------|------------------------------------------------------------------|
| Type | CH20M AD SHL 5.00/04 AG ... | Version |
| Order No. | 1472830000 | Hood, OMNIMATE Housing - series CH20M Agate grey, Side element |
| GTIN (EAN) | 4050118279429 | cover, Width: 22.5 mm |
| Qty. | 50 pc(s). | |
| Type | CH20M AD SHL 5.00/04 GG ... | Version |
| Order No. | 1413740000 | Hood, OMNIMATE Housing - series CH20M Graphite grey, Side |
| GTIN (EAN) | 4050118241648 | element cover, Width: 22.5 mm |
| Qty. | 50 pc(s). | |
| Type | CH20M AD SHL 5.00/04 BK ... | Version |
| Order No. | 1221310000 | Hood, OMNIMATE Housing - series CH20M black, Side element cover, |
| GTIN (EAN) | 4050118004830 | Width: 22.5 mm |
| Qty. | 50 pc(s). | |
| Type | CH20M AD SHL 5.00/04 LG ... | Version |
| Order No. | 1432890000 | Hood, OMNIMATE Housing - series CH20M Light Grey, Side element |
| GTIN (EAN) | 4050118237641 | cover, Width: 22.5 mm |
| Qty. | 50 pc(s). | |