

**FAD BLK 7 2HE20****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

The front adapters for migration are connected to the old PLC and, by means of a new pre-assembled cable, to the new one. Some adapters have 2 connectors for redundancy.

**General ordering data**

Order No.	<a href="#">1505530000</a>
Type	FAD BLK 7 2HE20
GTIN (EAN)	4050118319545
Qty.	1 pc(s).

## FAD BLK 7 2HE20

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	37 mm	Depth (inches)	1.457 inch
Height	24 mm	Height (inches)	0.945 inch
Width	209 mm	Width (inches)	8.228 inch
Net weight	187 g		

## Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

## Connection data

Connection (field side)	2 x Connector according IEC60603-13/DIN41651 20 p
-------------------------	---

## Ratings data

Operating voltage	50 V AC / 70 V DC
-------------------	-------------------

## Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 50 V AC
Surge voltage category	II	Pollution severity level	2
Pulse voltage test (1,2/50µs)	0.5 kV	Insulation test voltage AC	0.35 kV

## Classifications

ETIM 6.0	EC002584	ETIM 7.0	EC002584
ETIM 8.0	EC002584	ETIM 9.0	EC002584
ECLASS 9.0	27-33-02-92	ECLASS 9.1	27-24-22-92
ECLASS 10.0	27-33-02-92	ECLASS 11.0	27-33-02-92
ECLASS 12.0	27-33-02-92	ECLASS 13.0	27-33-02-92

## Approvals

Approvals



ROHS

Conform

## Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

## FAD BLK 7 2HE20

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

