

HSS 6.4-19.1 EL W30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

| | |
|--------------------|---|
| Version | Conductor and cable markers, 6.4 - 19.1 mm, white |
| Order No. | 1505900000 |
| Type | HSS 6.4-19.1 EL W30M |
| GTIN (EAN) | 4050118314380 |
| Qty. | 1 pc(s). |
| compatible printer | 2599430000 2599440000 |

HSS 6.4-19.1 EL W30M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|-----------|-----------------|--------------|
| Depth | 0.77 mm | Depth (inches) | 0.03 inch |
| Width | 30.9 mm | Width (inches) | 1.217 inch |
| Length | 30,000 mm | Length (inches) | 1,181.1 inch |
| Net weight | 285 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -55...135 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|---|-----------------------------------|-------------|
| Colour | white | Halogen | Yes |
| Length | 30,000 mm | Material | Polyolefine |
| Operating temperature range | -55...135 °C | Operating temperature range, max. | 135 °C |
| Operating temperature range, min. | -55 °C | Printed characters | without |
| Recommended industries | Plant manufacture, Energy, Device manufacturer, Machinery | Type of printing | neutral |
| Width | 30.9 mm | | |

Conductor and cable markers

| | | | |
|-----------------------------------|--------------------|----------------------------------|-------------------------|
| Conductor O.D. | 6.4 - 19.1 mm | Conductor O.D., max. | 19.1 mm |
| Conductor O.D., min. | 6.4 mm | Conductor cross-section, max. | 70 mm ² |
| Conductor cross-section, min. | 16 mm ² | Cross-section for connected wire | 16 - 70 mm ² |
| Halogen | Yes | Rate of shrinkage | 3:1 |
| Recommended shrinking temperature | 90 °C | Text field height | 30.7 mm |
| Text field width | 0 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Important note

| | |
|---------------------|---|
| Product information | External roll holder 1302920000 necessary |
|---------------------|---|

Approvals

Approvals



| | |
|-------------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (cURus) | E366310 |

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

Creation date May 21, 2024 11:47:19 PM CEST

Catalogue status 18.05.2024 / We reserve the right to make technical changes.

HSS 6.4-19.1 EL W30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



HSS 6.4-19.1 EL W30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | |
|------------|-----------------------------|------------|
| Type | RIBBON HSS HF EL 40/300 ... | Version |
| Order No. | 1426210000 | Ink ribbon |
| GTIN (EAN) | 4050118228823 | |
| Qty. | 1 pc(s). | |

THM MULTIMARK

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | |
|------------|----------------------------|
| Type | THM MMP ROLLER 30 |
| Order No. | 1357430000 |
| GTIN (EAN) | 4050118160253 |
| Qty. | 1 pc(s). |

| | |
|------------|----------------------------|
| Type | THM MMP EXT.RH |
| Order No. | 1302920000 |
| GTIN (EAN) | 4050118102307 |
| Qty. | 1 pc(s). |

| | |
|------------|----------------------------|
| Type | THM MMP ROLLER 115 |
| Order No. | 1357420000 |
| GTIN (EAN) | 4050118160314 |
| Qty. | 1 pc(s). |