

PAC-PREM-2X10-V1-2M5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the TER-MSERIES relay modules. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LiYY cable with a cross-section of 0.14mm².
- 10-pole flat cable connectors.

The cables are tested automatically for continuity and insulation to ensure the functionality for which they have been designed.

General ordering data

| | |
|------------|--|
| Version | Pre-assembled cable, PAC, Cable LiYY, 5.4 ± 1 mm |
| Order No. | 1512470025 |
| Type | PAC-PREM-2X10-V1-2M5 |
| GTIN (EAN) | 4032248413492 |
| Qty. | 1 pc(s). |

PAC-PREM-2X10-V1-2M5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | |
|------------|-------|
| Net weight | 206 g |
|------------|-------|

Temperatures

| | | | |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

General Data

| | | | |
|--------------------|----------------------|-----------------------|-----------------|
| Cable | Cable LiYY | Cable length | 2.5 m |
| Connector PLC side | HE10 20P | Interface connector | 2X HE10 10P |
| Material | PVC | Number of poles, min. | 10-pole |
| Outer diameter | 5.4 ± 1 mm | Suitable for | Digital signals |
| Wire cross-section | 0.14 mm ² | | |

Electrical Data

| | | | |
|---|----------|-------------------|------------|
| Capacity wire / wires | 300 pF/m | High voltage test | 1 KV/1s |
| Permissible current strength per path, max. | 1 A | Resistance | ≤ 150 mΩ/m |
| Total current, max. | 3 A | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000237 | ETIM 7.0 | EC000237 |
| ETIM 8.0 | EC000237 | ETIM 9.0 | EC000237 |
| ECLASS 9.0 | 27-24-22-20 | ECLASS 9.1 | 27-24-22-20 |
| ECLASS 10.0 | 27-24-22-20 | ECLASS 11.0 | 27-24-22-20 |
| ECLASS 12.0 | 27-24-22-20 | ECLASS 13.0 | 27-24-22-20 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|