

**HSS-HF 3.2-6.4 EL Y30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

Version	Conductor and cable markers, 3.2 - 6.4 mm, yellow
Order No.	<a href="#">1513180000</a>
Type	HSS-HF 3.2-6.4 EL Y30M
GTIN (EAN)	4050118321012
Qty.	1 pc(s).
compatible printer	<a href="#">2599430000</a> <a href="#">2599440000</a>

## HSS-HF 3.2-6.4 EL Y30M

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.9 mm	Depth (inches)	0.035 inch
Width	10.7 mm	Width (inches)	0.421 inch
Length	30,000 mm	Length (inches)	1,181.1 inch
Net weight	404 g		

## Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

## General data

Colour	yellow	Halogen	No
Length	30,000 mm	Material	Polyolefine
Number per roll	1	Operating temperature range	-55...105 °C
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Printed characters	without	Type of printing	neutral
Width	10.7 mm		

## Conductor and cable markers

Conductor O.D.	3.2 - 6.4 mm	Conductor O.D., max.	6.4 mm
Conductor O.D., min.	3.2 mm	Conductor cross-section, max.	6 mm <sup>2</sup>
Conductor cross-section, min.	1.5 mm <sup>2</sup>	Cross-section for connected wire	1.5 - 6 mm <sup>2</sup>
Halogen	No	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C		

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

## Important note

Product information	External roll holder 1302920000 necessary
---------------------	---

## Approvals

ROHS	Conform
------	---------

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">NFX 70-100-1 2006 + NF X 70-100-2 2006</a> <a href="#">BS EN ISO 4589-2 1999</a> <a href="#">EN 45545-2:2020</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**HSS-HF 3.2-6.4 EL Y30M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

