

ZQV 2.5N/50**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

Version	Cross-connector (terminal), Plugged, Number of poles: 50, Pitch in mm (P): 5.10, Insulated: Yes, 24 A, orange
Order No.	1527730000
Type	ZQV 2.5N/50
GTIN (EAN)	4050118411362
Qty.	5 pc(s).

ZQV 2.5N/50**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	24.7 mm	Depth (inches)	0.972 inch
Height	2.8 mm	Height (inches)	0.11 inch
Width	255 mm	Width (inches)	10.039 inch
Net weight	29.935 g		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-60 °C...130 °C
---------------------	----------------	-----------------------	-----------------

Material data

Material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

Additional technical data

Explosion-tested version	No	Type of fixing	Plugged
Type of mounting	Direct mounting		

Cross-connector

Number of cross-connected terminals	50
-------------------------------------	----

Dimensions

Pitch in mm (P)	5.1 mm
-----------------	--------

General

Number of poles	50
-----------------	----

Rating data

Rated current	24 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400V The voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Approvals

ROHS	Conform
------	---------

ZQV 2.5N/50

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Con-
formity

[Confirmation of Standards EN 45545-2_2020-10](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[Zuken E3.S](#)

User Documentation

[2434520000_BED-ANL_ZQV_A_REIHE.pdf](#)

[StorageConditionsTerminalBlocks](#)

[User Manual ZQV 2.5](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures