

**ZQV 4N/8****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

Version	Cross-connector (terminal), Plugged, Number of poles: 8, Pitch in mm (P): 6.10, Insulated: Yes, 32 A, orange
Order No.	<a href="#">1528030000</a>
Type	ZQV 4N/8
GTIN (EAN)	4050118332841
Qty.	20 pc(s).

**ZQV 4N/8****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	27.95 mm	Depth (inches)	1.1 inch
Height	2.8 mm	Height (inches)	0.11 inch
Width	46.5 mm	Width (inches)	1.831 inch
Net weight	5.75 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Operating temperature	-60 °C...130 °C
Continuous operating temp., min.	-60	Continuous operating temp., max.	130

**Material data**

Material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

**Additional technical data**

Explosion-tested version	Yes	Type of fixing	Plugged
--------------------------	-----	----------------	---------

**Cross-connector**

Number of cross-connected terminals	8	Rated current, 2-pole	32 A
Rated current, multi-pole	32 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	6.1 mm
-----------------	--------

**General**

Number of poles	8
-----------------	---

**Rating data**

Rated current	32 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

**Important note**

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	---

**ZQV 4N/8****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">DNVGL certificate</a> <a href="#">BV certificate</a> <a href="#">RINA certificate</a> <a href="#">Lloyds Register Certificate</a> <a href="#">Confirmation of Standards EN 45545-2_2020-10</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">2434520000_BED-ANL_ZQV_A_REIHE.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a> <a href="#">User Manual ZQV 2.5</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	