

**SFGH WM4 C BT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**WM4 C photovoltaic connectors**

- one crimp contact for 4 mm<sup>2</sup> and 6 mm<sup>2</sup> cables
- TÜV approval according to the latest standard IEC 62852
- Can be loaded with a rated current of up to 35 A

**General ordering data**

Version	Photovoltaics, Plug-in connector, male
Order No.	<a href="#">1530700000</a>
Type	SFGH WM4 C BT
GTIN (EAN)	4050118335330
Qty.	100 pc(s).

## SFGH WM4 C BT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	13.8 g
------------	--------

## Technical data

Approvals	TÜV Rheinland (IEC 62852)	Cable type	2 Pfg1169/08.07, EN 50618:2014
Conductor cross-section, max.	6 mm <sup>2</sup>	Conductor cross-section, min.	4 mm <sup>2</sup>
External thread	M 16	Outer cable diameter, max.	7 mm
Outer cable diameter, min.	5.5 mm	Pollution severity	2
Protection degree	IP65, IP67, IP2x open	Rated current	35 A
Rated voltage	1500 V DC (IEC)		

## Guarantee

Time interval	2 years
---------------	---------

## Classifications

ETIM 6.0	EC002928	ETIM 7.0	EC002928
ETIM 8.0	EC002928	ETIM 9.0	EC002928
ECLASS 9.0	22-57-92-03	ECLASS 9.1	27-44-01-07
ECLASS 10.0	27-44-01-07	ECLASS 11.0	22-57-02-92
ECLASS 12.0	22-57-02-92	ECLASS 13.0	22-57-02-92

## Important note

Product information	Please order contacts separately
---------------------	----------------------------------

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">WM4 C TÜV certificate</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">BPZL WM4C LANG</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>