

**CAN SUB-D M12 TERM PS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

**General ordering data**

Version	SUB-D
Order No.	<a href="#">1555280000</a>
Type	CAN SUB-D M12 TERM PS
GTIN (EAN)	4050118361094
Qty.	1 pc(s).

## CAN SUB-D M12 TERM PS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	16.8 mm	Depth (inches)	0.661 inch
Height	59 mm	Height (inches)	2.323 inch
Width	46.5 mm	Width (inches)	1.831 inch
Net weight	89 g		

## Temperatures

Humidity	Max. 75% at +25°C, non-condensing
----------	-----------------------------------

## Technical specifications for sub-D connector

BUS PG interface	D-Sub 9-pole, Pin	BUS interface	D-Sub 9-pole, Socket
BUS, cable interface	M12 A-coded, pin + socket	Data rate	1 Mbps
Housing main material	ZnAl	Humidity	Max. 75% at +25°C, non-condensing
Interlock	UNC4-40	Outgoing elbow	90°
Plugging cycles	≥ 200	Programming interface	Yes
Protection degree	IP30	Temperature range of housing	-20...+70 °C
Terminating resistor available	Yes		

## Classifications

ETIM 6.0	EC001132	ETIM 7.0	EC001132
ETIM 8.0	EC001132	ETIM 9.0	EC001132
ECLASS 9.0	27-44-03-02	ECLASS 9.1	27-44-03-90
ECLASS 10.0	27-44-03-02	ECLASS 11.0	27-44-03-02
ECLASS 12.0	27-44-03-02	ECLASS 13.0	27-44-03-02

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	3cc1d9b1-0f2a-47ed-a501-ddcfcfaaf625

## Approvals

ROHS	Conform
------	---------

## Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a>