

HSS-HF 1.2-2.4 EL Y75M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

| | |
|--------------------|---|
| Version | TwinMark, Conductor and cable markers, 1.2 - 2.4 mm, yellow |
| Order No. | 1562640000 |
| Type | HSS-HF 1.2-2.4 EL Y75M |
| GTIN (EAN) | 4050118371550 |
| Qty. | 1 pc(s). |
| compatible printer | 2599430000 2599440000 |

HSS-HF 1.2-2.4 EL Y75M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|-----------|-----------------|---------------|
| Depth | 0.5 mm | Depth (inches) | 0.02 inch |
| Width | 4.2 mm | Width (inches) | 0.165 inch |
| Length | 75,000 mm | Length (inches) | 2,952.75 inch |
| Net weight | 208 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -55...105 °C |
|-----------------------------|--------------|

General data

| | | |
|--------------------------------------|--|--------------------|
| Colour | yellow | |
| Halogen | No | |
| Length | 75,000 mm | |
| Material | Polyolefine | |
| Number of markers per combination | 1 Shrink sleeve reel = Conductor and cable markers | |
| Number of markers per packaging unit | Form of supply | Shrink sleeve reel |
| Number per roll | 1 | |
| Operating temperature range | -55...105 °C | |
| Operating temperature range, max. | 105 °C | |
| Operating temperature range, min. | -55 °C | |
| Printed characters | without | |
| Type of printing | neutral | |
| Width | 4.2 mm | |

Conductor and cable markers

| | | | |
|-----------------------------------|----------------------|----------------------------------|----------------------------|
| Conductor O.D. | 1.2 - 2.4 mm | Conductor O.D., max. | 2.4 mm |
| Conductor O.D., min. | 1.2 mm | Conductor cross-section, max. | 0.5 mm ² |
| Conductor cross-section, min. | 0.25 mm ² | Cross-section for connected wire | 0.25 - 0.5 mm ² |
| Halogen | No | Rate of shrinkage | 2:1 |
| Recommended shrinking temperature | 90 °C | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Important note

| | |
|---------------------|---|
| Product information | External roll holder 1302920000 necessary |
|---------------------|---|

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | NFX 70-100-1 2006 + NF X 70-100-2 2006 BS EN ISO 4589-2 1999 EN 45545-2:2020 |
| Catalogues | Catalogues in PDF-format |

Creation date May 2, 2024 1:30:31 PM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

HSS-HF 1.2-2.4 EL Y75M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | |
|------------|-----------------------------|------------|
| Type | RIBBON HSS HF EL 40/300 ... | Version |
| Order No. | 1426210000 | Ink ribbon |
| GTIN (EAN) | 4050118228823 | |
| Qty. | 1 pc(s). | |

THM MULTIMARK

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | |
|------------|----------------------------|
| Type | THM MMP ROLLER 115 |
| Order No. | 1357420000 |
| GTIN (EAN) | 4050118160314 |
| Qty. | 1 pc(s). |

| | |
|------------|----------------------------|
| Type | THM MMP ROLLER 30 |
| Order No. | 1357430000 |
| GTIN (EAN) | 4050118160253 |
| Qty. | 1 pc(s). |

| | |
|------------|----------------------------|
| Type | THM MMP EXT.RH |
| Order No. | 1302920000 |
| GTIN (EAN) | 4050118102307 |
| Qty. | 1 pc(s). |

HSS-HF 1.2-2.4 EL Y75M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

Accessories

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | |
|------------|----------------------------|
| Type | MM PLUS ROLLER 110 |
| Order No. | 2672590000 |
| GTIN (EAN) | 4050118708097 |
| Qty. | 1 pc(s). |