

**KLBUE 10-20****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****Shielding and earthing**

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

**General ordering data**

Version	Clamping yoke, Clamping yoke, Steel
Order No.	<a href="#">1600490000</a>
Type	KLBUE 10-20
GTIN (EAN)	4008190151874
Qty.	10 pc(s).

## KLBUE 10-20

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	40 mm	Depth (inches)	1.575 inch
Height	26 mm	Height (inches)	1.024 inch
Width	24 mm	Width (inches)	0.945 inch
Net weight	29.848 g		

## Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

## Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

## System specifications

Version	For a shield connection
---------	-------------------------

## Additional technical data

Explosion-tested version	Yes	Installation advice	Busbar
Type of fixing	Snap-on		

## Conductors for clamping (rated connection)

Cable diameter, max.	20 mm	Cable diameter, min.	10 mm
----------------------	-------	----------------------	-------

## Dimensions

Pitch in mm (P)	25 mm
-----------------	-------

## General

Installation advice	Busbar
---------------------	--------

## Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ETIM 9.0	EC002020
ECLASS 9.0	27-14-11-50	ECLASS 9.1	27-14-11-50
ECLASS 10.0	27-14-11-50	ECLASS 11.0	27-14-11-50
ECLASS 12.0	27-14-11-50	ECLASS 13.0	27-25-01-20

## Approvals

ROHS	Conform
------	---------

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Attestation of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Beipackzettel_KLBUE.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

Creation date May 2, 2024 1:49:26 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

## KLBUE 10-20

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Mounting support



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

## General ordering data

Type	WSH 5	Version
Order No.	<a href="#">1080100000</a>	Accessories, Rail support, Wemid
GTIN (EAN)	4008190965143	
Qty.	10 pc(s).	
Type	WSH 3/H/N	Version
Order No.	<a href="#">1715970000</a>	Accessories, Rail support, Wemid
GTIN (EAN)	4008190353100	
Qty.	10 pc(s).	
Type	WSH 6	Version
Order No.	<a href="#">1080200000</a>	Accessories, Rail support, Wemid
GTIN (EAN)	4008190965150	
Qty.	10 pc(s).	
Type	WSH 1	Version
Order No.	<a href="#">1068700000</a>	Accessories, Rail support, PA 66 GF 30
GTIN (EAN)	4008190118389	
Qty.	10 pc(s).	

## Copper



Of all the metals used, copper has the best electrical conductivity, which results in the highest short-circuit resistance. This makes the copper busbar the most widely used variant.

## General ordering data

Type	SSCH 10X3X1000 CU/SN	Version
Order No.	<a href="#">0348900000</a>	Busbar (terminal)
GTIN (EAN)	4008190024802	
Qty.	1 m	