

WKB 1/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The short current bridges are inserted into two instrument transformer wiring terminal blocks. By using the short-circuit bridge, the desired short-circuit could be realized within the application for maintenance work.

General ordering data

Version	Cross-connector (terminal), Plugged, Number of poles: 10, Pitch in mm (P): 8.00, Insulated: Yes, 4 1 A, orange
Order No.	1604330000
Type	WKB 1/10
GTIN (EAN)	4008190129576
Qty.	20 pc(s).

Technical data**Dimensions and weights**

Depth	6.1 mm	Depth (inches)	0.24 inch
Height	9.3 mm	Height (inches)	0.366 inch
Width	77.3 mm	Width (inches)	3.043 inch
Net weight	7.525 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	Polyamide 66	Colour	orange
UL 94 flammability rating	V-2		

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Plugged	Type of mounting	when screwed in

Dimensions

Pitch in mm (P)	8 mm
-----------------	------

General

Installation advice	Direct mounting	Number of poles	10
Operating temperature range, max.	100 °C		

Rating data

Rated current	41 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Approvals

ROHS	Conform
------	---------

Technical data

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	