

**ZQV 2.5/6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

Version	Accessories, Cross-connector, 24 A
Order No.	<a href="#">1608900000</a>
Type	ZQV 2.5/6
GTIN (EAN)	4008190149840
Qty.	20 pc(s).

**ZQV 2.5/6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	27.6 mm	Depth (inches)	1.087 inch
Height	28.9 mm	Height (inches)	1.138 inch
Width	2.8 mm	Width (inches)	0.11 inch
Net weight	3.75 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60
Continuous operating temp., max.	130		

**Material data**

Material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

**System specifications**

Version	For the terminals
---------	-------------------

**Additional technical data**

Explosion-tested version	Yes	Installation advice	Direct mounting
Type of fixing	Plugged		

**Cross-connector**

Number of cross-connected terminals	6	Rated current, 2-pole	24 A
Rated current, multi-pole	24 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	5.1 mm
-----------------	--------

**General**

Installation advice	Direct mounting	Number of poles	6
---------------------	-----------------	-----------------	---

**Rating data**

Rated current	24 A
---------------	------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

**Important note**

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	---

## ZQV 2.5/6

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">Confirmation of Standards EN 45545-2_2020-10</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">Operating instructions_ZDU1.5-ZDU35_ZQV.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a> <a href="#">User Manual ZQV 2.5</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	