

**SKMU PG11-MS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	SKMU MS (brass locknut), Locknut, PG 11, 3 mm, Brass, nickel-plated
Order No.	<a href="#">1694090000</a>
Type	SKMU PG11-MS
GTIN (EAN)	4008190872250
Qty.	100 pc(s).

**SKMU PG11-MS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	3 mm	Height (inches)	0.118 inch
Net weight	2.3 g		

**General information**

AF size 1	21 mm	Cable glands	PG 11
External thread	PG 11	Halogen	No
Internal thread	PG 11	Length of thread	3 mm
Material	Brass, nickel-plated	O.D.	24.26 mm
Pitch of thread	1.41 mm	Thickness	3 mm

**Classifications**

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ETIM 9.0	EC000940
ECLASS 9.0	27-14-44-24	ECLASS 9.1	27-14-44-24
ECLASS 10.0	27-14-44-24	ECLASS 11.0	27-14-44-24
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

### SKMU PG11-MS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

