

DFFC 0.2-0.35 ZRV1.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Integrate, expand and customise: the perfect supplement to every application.

Universal system accessories enable easy adaptation of the interfaces to fulfil specific requirements for the relevant application.

General ordering data

Version	Crimp contact (terminal), 0.35 mm ²
Order No.	1705310000
Type	DFFC 0.2-0.35 ZRV1.5
GTIN (EAN)	4008190948573
Qty.	500 pc(s).

DFFC 0.2-0.35 ZRV1.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	0.21 g
------------	--------

Temperatures

Operating temperature	130 °C
-----------------------	--------

System parameters

Product family	Accessories
----------------	-------------

Material data

Colour	silver	Colour chart (similar)	RAL 7001
Operating temperature, max.	130 °C		

Packing

VPE length	120 mm	VPE width	79 mm
VPE height	29 mm		

Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ETIM 9.0	EC000796
ECLASS 9.0	27-44-02-04	ECLASS 9.1	27-44-02-04
ECLASS 10.0	27-44-02-04	ECLASS 11.0	27-44-02-04
ECLASS 12.0	27-44-02-04	ECLASS 13.0	27-44-02-04

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Declaration of the Manufacturer
Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	