

**WSM 10 0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

**WSM small plates**

- Completely rust-free and acid-resistant
- Embossed characters are still legible when painted
- Also available with custom printing, embossed on a carrier
- Contents of the WSM Service Box, 40 each of: 0-9, A-Ö, +, -, x, /, :, ., ~, =, ü, Earth, Neutral. 200 steel cable ties (200 mm). 30 stainless steel carriers, 48 mm and 60 mm; 20 steel carriers, 84 mm, and 10 steel carriers, 108 mm and 288 mm

**General ordering data**

Version	Stainless steel markers, Conductor and cable markers, 5.5 x 9.9 mm, silver
Order No.	<a href="#">1712501000</a>
Type	WSM 10 0
GTIN (EAN)	4008190947187
Qty.	200 pc(s).

**WSM 10 0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	0.3 mm	Depth (inches)	0.012 inch
Height	5.5 mm	Height (inches)	0.217 inch
Width	9.9 mm	Width (inches)	0.39 inch
Net weight	0.13 g		

**Temperatures**

Operating temperature range	500 °C
-----------------------------	--------

**General data**

Colour	silver	
Halogen	No	
Material	Stainless steel 1.4404	
Material colour according to resistance code	0	
Number of markers per combination	1 Component part = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	Component part
Operating temperature range	500 °C	
Operating temperature range, max.	500 °C	
Orientation of print	horizontal	
Printed characters	Numbers	
Printing	0	
Type of printing	Standard	
Width	9.9 mm	

**Conductor and cable markers**

Conductor cross-section, max.	500 mm <sup>2</sup>	Conductor cross-section, min.	16 mm <sup>2</sup>
Cross-section for connected wire	16 - 500 mm <sup>2</sup>	Halogen	No

**Classifications**

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

## WSM 10 0

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Cable tie tools



## General ordering data

Type	WSM TOOL AUTOMATIK	Version
Order No.	<a href="#">1774470000</a>	Stainless steel markers, Conductor and cable markers, 180 x 275 mm,
GTIN (EAN)	4032248149261	silver
Qty.	1 pc(s).	
Type	WSM TOOL MANUELL	Version
Order No.	<a href="#">1774480000</a>	Stainless steel markers, Conductor and cable markers, 210 x 220 mm,
GTIN (EAN)	4032248149278	silver
Qty.	1 pc(s).	

## Stainless steel



Weidmüller stainless steel Series contains a comprehensive assortment of stainless steel cable ties for extreme conditions such as high temperatures or severe chemical effects.

- stainless steel AISI 316,
- ideal for use outdoors,
- radiation- and corrosion-resistant,
- anti-magnetic,
- no serrations, so no damage to the insulation.

## General ordering data

Type	SCT 4.6/360 C	Version
Order No.	<a href="#">1699910000</a>	Cable ties, 4.6 x 360 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892357	
Qty.	100 pc(s).	
Type	SCT 4.6/127 C	Version
Order No.	<a href="#">1699800000</a>	Cable ties, 4.6 x 127 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892241	
Qty.	100 pc(s).	
Type	SCT 4.6/266 C	Version
Order No.	<a href="#">1699900000</a>	Cable ties, 4.6 x 266 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892340	
Qty.	100 pc(s).	
Type	SCT 4.6/201 C	Version
Order No.	<a href="#">1699810000</a>	Cable ties, 4.6 x 201 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892258	
Qty.	100 pc(s).	

## WSM 10 0

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	SCT 4.6/838	Version
Order No.	<a href="#">1699940000</a>	Cable ties, 4.6 x 838 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892388	
Qty.	100 pc(s).	
Type	SCT 4.6/679	Version
Order No.	<a href="#">1699930000</a>	Cable ties, 4.6 x 679 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892371	
Qty.	100 pc(s).	
Type	SCT 4.6/520	Version
Order No.	<a href="#">1699920000</a>	Cable ties, 4.6 x 520 mm, Stainless steel 1.4301, 445 N
GTIN (EAN)	4008190892364	
Qty.	100 pc(s).	

## Holder



WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

**Advantages:**

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

## General ordering data

Type	WSMH 48MM	Version
Order No.	<a href="#">1774500000</a>	Stainless steel markers, Conductor and cable markers, 48 x 11 mm,
GTIN (EAN)	4032248149292	silver
Qty.	50 pc(s).	
Type	WSMH 108MM	Version
Order No.	<a href="#">1774530000</a>	Stainless steel markers, Conductor and cable markers, 108 x 11 mm,
GTIN (EAN)	4032248149322	silver
Qty.	50 pc(s).	
Type	WSMH 288MM	Version
Order No.	<a href="#">1774490000</a>	Stainless steel markers, Conductor and cable markers, 288 x 11 mm,
GTIN (EAN)	4032248149285	silver
Qty.	50 pc(s).	
Type	WSMH 60MM	Version
Order No.	<a href="#">1774510000</a>	Stainless steel markers, Conductor and cable markers, 60 x 11 mm,
GTIN (EAN)	4032248149308	silver
Qty.	50 pc(s).	
Type	WSMH 84MM	Version
Order No.	<a href="#">1774520000</a>	Stainless steel markers, Conductor and cable markers, 84 x 11 mm,
GTIN (EAN)	4032248149315	silver
Qty.	50 pc(s).	