

GWDR PG13,5-PO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 13.5, Polyethylene
Order No.	1719470000
Type	GWDR PG13,5-PO
GTIN (EAN)	4008190352721
Qty.	100 pc(s).

GWDR PG13,5-PO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	2 mm	Height (inches)	0.079 inch
Net weight	0.27 g		

Temperatures

Operating temperature	-30 °C...90 °C
-----------------------	----------------

General information

Cable glands	PG 13.5	Diameter of sealing ring	25 mm
External thread	PG 13.5	Inside diameter D2	20.4 mm
Internal thread	PG 13.5	Material	Polyethylene
Number of wires	1	O.D.	25 mm
Operating temperature range, max.	90 °C	Operating temperature range, min.	-30 °C
Sealing	PE-HD	Silicone	Yes
Thickness	2 mm		

Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ETIM 9.0	EC001181
ECLASS 9.0	27-43-03-19	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-43-03-19	ECLASS 11.0	27-43-03-19
ECLASS 12.0	27-43-03-19	ECLASS 13.0	27-43-03-19

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

GWDR PG13,5-PO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

