

GWDR PG36-NP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	GWDR NP (flat gasket - neoprene), Sealing ring, PG 36, Neoprene
Order No.	1719610000
Type	GWDR PG36-NP
GTIN (EAN)	4008190352875
Qty.	20 pc(s).

GWDR PG36-NP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	1.5 mm	Height (inches)	0.059 inch
Net weight	3 g		

Temperatures

Operating temperature	-40 °C... 100 °C
-----------------------	------------------

General information

Cable glands	PG 36	Diameter of sealing ring	60 mm
External thread	PG 36	Halogen	Yes
Inside diameter D2	47 mm	Internal thread	PG 36
Material	Neoprene	Number of wires	1
O.D.	60 mm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Sealing	Neoprene
Silicone	No	Thickness	1.5 mm

Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ETIM 9.0	EC001181
ECLASS 9.0	27-43-03-19	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-43-03-19	ECLASS 11.0	27-43-03-19
ECLASS 12.0	27-43-03-19	ECLASS 13.0	27-43-03-19

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

GWDR PG36-NP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

