

EWS PG16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	EWS (drainage device), Compensating element, PG 16, 5 mm, Polyamide
Order No.	1719730000
Type	EWS PG16
GTIN (EAN)	4008190352998
Qty.	20 pc(s).

EWS PG16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	23 mm	Length (inches)	0.906 inch
Net weight	12.75 g		

Temperatures

Operating temperature	-20 °C...40
-----------------------	-------------

Certificate numbers cable gland

Certificate no. cable gland (ATEX)	PTB 01 ATEX 1128 X	Identification	Ex e II, II 2 GD
------------------------------------	--------------------	----------------	------------------

General information

AF size 1	27 mm	Cable glands	PG
External thread	PG 16	Length of thread	5 mm
Material	Polyamide	Operating temperature range, max.	40 °C
Operating temperature range, min.	-20 °C	Protection degree	IP54
Torque for connecting adapter, max.	5 Nm	Torque for connecting adapter, min.	5 Nm
UL 94 flammability rating	V-2		

Classifications

ETIM 6.0	EC000814	ETIM 7.0	EC000814
ETIM 8.0	EC000814	ETIM 9.0	EC000814
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-18-28-17	ECLASS 13.0	27-18-28-17

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

EWS PG16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

