

EWS M 25X1,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	EWS (drainage device), Compensating element, M 25, 5 mm, Polyamide
Order No.	1719740000
Type	EWS M 25X1,5
GTIN (EAN)	4008190353001
Qty.	20 pc(s).

EWS M 25X1,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	23 mm	Length (inches)	0.906 inch
Net weight	13.25 g		

Temperatures

Operating temperature	-20 °C...40
-----------------------	-------------

Certificate numbers cable gland

Certificate no. cable gland (ATEX)	PTB 01 ATEX 1128 X	Identification	Ex e II, II 2 GD
------------------------------------	--------------------	----------------	------------------

General information

AF size 1	30 mm	Cable glands	metric
External thread	M 25	Length of thread	5 mm
Material	Polyamide	Operating temperature range, max.	40 °C
Operating temperature range, min.	-20 °C	Pitch of thread	1.5 mm
Protection degree	IP54	Torque for connecting adapter, max.	5 Nm
Torque for connecting adapter, min.	5 Nm	UL 94 flammability rating	V-2

Classifications

ETIM 6.0	EC000814	ETIM 7.0	EC000814
ETIM 8.0	EC000814	ETIM 9.0	EC000814
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-18-28-17	ECLASS 13.0	27-18-28-17

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

EWS M 25X1,5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

