

SZS M20**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SZS (serrated washer), Retaining toothed washers, M 20, Stainless steel 1.4404 (316L)
Order No.	1736310000
Type	SZS M20
GTIN (EAN)	4008190963514
Qty.	10 pc(s).

SZS M20**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	4.5 mm	Height (inches)	0.177 inch
Net weight	5.13 g		

General information

Cable glands	metric	External thread	M 20
Halogen	halogen-free	Inside diameter D2	21.3 mm
Internal thread	M 20	Material	Stainless steel 1.4404 (316L)
O.D.	32.4 mm	Pitch of thread	1.5 mm
Thickness	1.5 mm		

Classifications

ETIM 6.0	EC002345	ETIM 7.0	EC002345
ETIM 8.0	EC002345	ETIM 9.0	EC002345
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-07	ECLASS 13.0	27-14-08-07

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

SZS M20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

