

EA-RING MS/M 20**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	EA (earthing rings), Earthing ring, Miscellaneous, M 20, Brass, nickel-plated
Order No.	1736490000
Type	EA-RING MS/M 20
GTIN (EAN)	4008190963590
Qty.	20 pc(s).

EA-RING MS/M 20**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	53.8 mm	Height (inches)	2.118 inch
Length	53.8 mm	Length (inches)	2.118 inch
Net weight	6.95 g		

Certificate numbers cable gland

Identification	Ex e II, II 2 GD, EEx d II
----------------	----------------------------

General information

Cable glands	M 20	External thread	M 20
Gap, internal dimension B	33 mm	Inside diameter D2	7 mm
Material	Brass, nickel-plated	O.D.	28.6 mm
Thickness	1.5 mm	Width, outer dimension C	13 mm

Classifications

ETIM 6.0	EC002317	ETIM 7.0	EC002317
ETIM 8.0	EC002317	ETIM 9.0	EC002317
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-07	ECLASS 13.0	27-14-08-07

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	2bd73422-c6ea-4a92-b8e7-00964d1156f3

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

EA-RING MS/M 20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

