

**EA-RING MS/M 50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

|            |   |
|------------|---|
| Version    | EA (earthing rings), Earthing ring, Miscellaneous, M 50, Brass, nickel-plated |
| Order No.  | <a href="#">1736530000</a>  |
| Type       | EA-RING MS/M 50   |
| GTIN (EAN) | 4008190963644   |
| Qty.       | 10 pc(s).   |

**EA-RING MS/M 50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |          |                 |           |
|------------|----------|-----------------|-----------|
| Height     | 111.5 mm | Height (inches) | 4.39 inch |
| Length     | 111.5 mm | Length (inches) | 4.39 inch |
| Net weight | 38 g     |                 |           |

**Certificate numbers cable gland**

|                |                            |
|----------------|----------------------------|
| Identification | Ex e II, II 2 GD, EEx d II |
|----------------|----------------------------|

**General information**

|                           |                      |                          |         |
|---------------------------|----------------------|--------------------------|---------|
| Cable glands              | M 50                 | External thread          | M 50    |
| Gap, internal dimension B | 58 mm                | Inside diameter D2       | 13.5 mm |
| Material                  | Brass, nickel-plated | O.D.                     | 67 mm   |
| Thickness                 | 1.5 mm               | Width, outer dimension C | 40 mm   |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002317    | ETIM 7.0    | EC002317    |
| ETIM 8.0    | EC002317    | ETIM 9.0    | EC002317    |
| ECLASS 9.0  | 27-14-44-32 | ECLASS 9.1  | 27-14-44-90 |
| ECLASS 10.0 | 27-14-44-32 | ECLASS 11.0 | 27-14-44-32 |
| ECLASS 12.0 | 27-14-08-07 | ECLASS 13.0 | 27-14-08-07 |

**Environmental Product Compliance**

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | 2bd73422-c6ea-4a92-b8e7-00964d1156f3 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
| Brochures  |  |

## EA-RING MS/M 50

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

