

**KSP L24****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	KSP (Klippon shroud), Protective cap, PVC
Order No.	<a href="#">1736570000</a>
Type	KSP L24
GTIN (EAN)	4008190956226
Qty.	10 pc(s).
Delivery status	<b>This article will no longer be available in the future.</b>
Available until	2023-07-30

**KSP L24****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	120 mm	Height (inches)	4.724 inch
Length	123 mm	Length (inches)	4.843 inch
Wall thickness, min.	2 mm	Wall thickness, max.	2 mm
Net weight	21.1 g		

**Temperatures**

Operating temperature	-25 °C...70 °C
-----------------------	----------------

**General information**

Gap, internal dimension B	70 mm	Halogen	No
Hardness (Shore A)	65	Inside diameter D2	25 mm
Material	PVC	O.D.	29 mm
Operating temperature range, max.	70 °C	Operating temperature range, min.	-25 °C
Silicone	No	Thickness	2 mm

**Classifications**

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-07	ECLASS 13.0	27-14-08-07

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## KSP L24

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

